

SNP810C2



Article Number: 190-00224

Snapper Hose Clamps, .514"/.587" Min/Max Diameter, POM, White, 100/pkg



Download spec sheet

Base Data

Local Order Number SNP810C2
Type SNP8
Color White (WH)

Features and Benefits

- Designed for quick, ratcheted installation and can be released and reused.
- Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.

Product Description HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

Short Description Snapper Hose Clamps, .514"/.587" Min/Max Diameter, POM, White, 100/pkg

Product Dimensions

Fixation Method Plug-in mounting
Variant Closed
Width W2 (Imperial) 0.229 "
Width W2 (Metric) 5.82 mm
Diameter Min. (Imperial) 0.514 "
Diameter Min. (Metric) 13.06 mm
Diameter Max. (Imperial) 0.587 "
Diameter Max. (Metric) 14.91 mm
Wall Thickness WT (Imperial) 0.069 "
Wall Thickness WT (Metric) 1.8 mm

Logistics and Packaging

Quantity Per bag
Package Quantity (Metric) 100
Carton Quantity 5000

Material and Specifications

Material Polyacetal (POM)
Material Shortcut POM
Flammability UL94 HB
Operating Temperature -40°F to +185°F (-40°C to +85°C)
ROHS Compliant Yes

