

## T30R9M4



**Article Number:** 111-03047

**Standard Cable Tie, 5.8" Long, 30lb Tensile Strength, PA66, Natural, 1000/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** T30R9M4

**Type** T30R

**Color** Natural (NA)

- Features and Benefits**
- Inside serrations allow for strong hold on cables and wire bundles.
  - Head design provides high tensile strength with very low insertion force.
  - Bent tail ensures a quick and simple installation.

**Product Description** HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** Standard Cable Tie, 5.8" Long, 30lb Tensile Strength, PA66, Natural, 1000/pkg

### Product Dimensions

**Minimum Tensile Strength (Imperial)** 30.0 lbs

**Minimum Tensile Strength (Metric)** 135.0 N

**Length L (Imperial)** 5.8 "

**Length L (Metric)** 148.0 mm

**Fixation Method** None

**Identification Plate Position** none

**Releasable Closure** No

**Tie Closure** plastic pawl

**Variant** Inside Serrated

**Width W (Imperial)** 0.14 "

**Width W (Metric)** 3.6 mm

**Bundle Diameter Min. (Imperial)** 0.06 "

**Bundle Diameter Min. (Metric)** 1.5 mm

**Bundle Diameter Max. (Imperial)** 1.38 "

**Bundle Diameter Max. (Metric)** 35.0 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 1000

**Carton Quantity** 5000

**Weight (Metric)** 0.7 kg

## Material and Specifications

---

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>US MILSPEC</b>	MS3367-5-9
<b>Flammability</b>	UL94 V2
<b>Halogenfree</b>	Yes
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	Cage Code 53421 UL-ZODZ E64139 SAE - AS33671
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes