
KEMET Part Number: SMR5102J50J01L16.5CBULK

(F211JF102J050ALG5C)



Capacitor, film, Metallized PPS, 1000 pF, +/-5% Tol, -55/+150C, General Purpose, 50 VDC@125C, Lead Spacing=5 mm



Dimensions (mm)			
Symbol	Dimension	Tolerance	
L	7.2	MAX	
Н	6.5	MAX	
Т	2.5	MAX	
S	5	+/-0.4	
LL	16.5	+/-0.5	
G	0.5	NOM	
F	0.5	+/-0.05	

Notes:	
-Case Size = JF	

General Information		
Supplier:	KEMET	
Dielectric:	Metallized PPS	
Application:	General Purpose	
Style:	Radial Box	
Lead Form:	Wire Leads	
RoHS:	Yes	

Specifications	
Capacitance:	1000 pF
Voltage:	50 VDC
Tolerance:	+/-5%
Voltage AC:	30 VAC
Rated Temperature:	125C
Temperature Range:	-55/+150C
Dissipation Factor @ 1 kHz:	0.15%
Dissipation Factor @ 10 kHz:	0.25%
Dissipation Factor @ 100kHz:	0.6%
Insulation Resistance:	15 GOhm
Maximum dVdT:	40 v/us
Miscellaneous:	The rated voltage decreases 2%/ C between +125C and +150C

Packaging Specifications		
Package Kind:	Bulk	
Package Quantity:	2000	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

