

ETST666



Article Number: 904-00022

Electrical Tape, Thickness 7.0 mil, PVC, Blue, 10 Rolls/pkg



Download spec sheet

Base Data

Local Order Number ETST666

Type ETST66

Color Blue (BU)

Features and Benefits

- PVC Tape is ideal for general purpose electrical applications.
- Heavy duty tape is comfortable and has exceptional surface and adhesive characteristics.
- Fast, easy and economical way to color coding, cable splicing, terminating and wire insulating.

Product Description Electrical tapes are heavy duty vinyl and ideal for general purpose applications. Tape provides a fast, easy and economical way to cable splicing, terminating, wire insulating, and more. These comfortable high quality tapes have exceptional surface and adhesive characteristics. Tape is applied by overlapping each layer 50% and using tension. After the tape is adhered, the memory of the tape returns, tightening the seal and making the taped area even more waterproof.

Short Description Electrical Tape, Thickness 7.0 mil, PVC, Blue, 10 Rolls/pkg

Product Dimensions

Length L (Imperial) 66.0 ft

Length L (Metric) 20.12 m

Width W (Imperial) 0.75 "

Width W (Metric) 19.05 mm

Thickness T (Imperial) 7.0 mil

Logistics and Packaging

Quantity Per reel

Package Quantity 10

Package Quantity (Metric) 10

Carton Quantity 200

Material and Specifications

Material Flexible Polyvinyl Chloride (PVC)

Material Shortcut PVC

US MILSPEC MIL-1-7798-A

Adhesion 16 oz./inch

Operating Temperature +20°F to 176°F (-7°C to +80°C)

UL Listed (US and Canada) No

UL Listed (US) Yes

UL Recognized (US) Yes

UL Recognized (US and Canada) No

© HellemannTyton 2015