

PROSAFE ALUMINIUM LED PENLIGHT



10
HOURS
RUNTIME

45
METRE
BEAM RANGE

110
LUMENS
OUTPUT

IPX4
WATER
RESISTANCE

- » 110 Lumen white 1W LG LED
- » Convenient detachable pocket clip
- » Tactical rubberised micro switch
- » Multi-faceted reflector for smooth beam
- » Die cast aluminium housing
- » Ultra clear AR coated glass lens
- » Impact resistant to 1M
- » IPX4 water resistant
- » Lightweight and portable

BATTERY 2 x 1.5v AAA Duracell Alkaline (included)

WEIGHT 46g (with batteries)

DIMENSION 14 x 131mm



CONVENIENT POCKET CLIP



2 X AAA BATTERIES (INC)



MULTI-FACETED REFLECTOR



TACTICAL RUBBERISED SWITCH