

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191640080**
Status: **Active**
Overview: Perma-Seal™ Terminals
Description: Perma-Seal™ Ring Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5)

Documents:

3D Model Product Specification PS-19902-013 (PDF)
Drawing (PDF) RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011 (PDF)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series 19164
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview Perma-Seal™ Terminals
 Product Name Perma-Seal™
 Type Ring
 UPC 800753113640

Physical

Barrel Type Closed
 Insulation NiAc™
 Material - Plating Mating Tin
 Net Weight 1.460/g
 Packaging Type Bag
 Stud Size 10 (M5)
 Wire Insulation Diameter 9.53mm
 Wire Size AWG 8
 Wire Size mm² 7.96

Material Info

Old Part Number SD-656-10

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
 Sales Drawing SD-19164-023



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

19164 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	<u>0640055400</u>
Hand Crimp Tool	<u>0640013900</u>