



ISSUES	
5	11.7.89 REDEMAN
6	DIP 1480 ADDED ELC 0632

TYPE	L'	USG PIN	PO °C/W
DIP 1495	30,5	24 PIN	25,0
DIP 1496	36,0	28 PIN	22,0
DIP 1497	50,8	40 PIN	19,7
DIP 1498	61,0	48 PIN	18,3
DIP 1499	81,3	64 PIN	16,4
DIP 1480	116,0		

GENERAL TOLERANCES TO
REDPOINT STANDARDS
EXTRUSION REG A3633

DO NOT SCALE

REDPOINT LTD. OWNS THE COPYRIGHT OF THIS DOCUMENT WHICH IS SUPPLIED IN CONFIDENCE AND WHICH MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED AND MUST NOT BE REPRODUCED WITHOUT PERMISSION IN WRITING FROM THE OWNERS.

<p>THIRD ANGLE</p>	Material	<p>TOLERANCES</p> <p>Fractions + 1/64"</p> <p>Decimals ± .005"</p> <p>Metric ± .125mm</p> <p>UNLESS OTHERWISE SPECIFIED</p>
	Treatment	
	Finish	

redpoint limited		
Title <u>DIP 1495-1499 HEATSINKS</u>		
Drg. No. <u>2A2673</u>	Scale <u>NT</u>	Date <u>11.7.89</u>