

PRODUCT SPECIFICATION

Item #	Farnell UK Item #	Description	MOQ	Carton Quantity	N.W	G.W	CUFT
NT-8540		Laser Distance Measurer(40M)	20 PCS	20 PCS	5.5 kgs	6.5 kgs	1.549



Features

Outdoor / Indoor use

Complies with IP54 rated as dust-protection and spray-pooof

Extra side key

One touch extra side key for using easily and quickly

Integrated multi-measuring functions

Area, Volume, Pythagorean measurement allows easy measuring in any different applications

LCD display

Comes with large LCD display with backlight allows for data reading in dark areas

Fold-out extension

At bottom provides more convenient with reference point

Specifications

Model name	NT-8540
Measuring range	0.2~40M
Measuring accuracy	±1.5mm
LCD display	4 line display with backlight
Length / Area / Volume measurement	Yes
Continuous/ Min,Mix measurement	Yes
Pythagorean 1 / Pythagorean 2	Yes
Add/Subtraction	Yes
Data Memory	20 record
Unit Selection	M / ft / in / ft+in
Beep indicate	Yes
Auto power off	After 3min.
Auto Laser power off	30s
Low battery indicate	Y
Laser class	Class 2
Laser Power	635 nm≤1mW
Operation temperature	0°C -40°C
Storage temperature	-10°C -60°C
Power source	2 x 1.5V AAA batteries (not included)
Weight	113g (not including battery)
Dimension	115 x 52 x 32.5

***** Picture for reference only. All specifications are subject to change by supplier. *****

Individual packing: Color box

~ THE END ~