

Product type designation

PROFIBUS bus connector, RS485, Fast Connect, without PG socket, 35°

Product description

PROFIBUS bus connector, RS485, Fast Connect, without PG socket, 35°
SIMATIC DP, BUS CONNECTOR FOR PROFIBUS UP TO 12 MBIT/S 35 DEGREE ANGLE CABLE OUTLET, IPCD TECHNOLOGY FAST CONNECT, WITHOUT PG SOCKET 15,8 X 54 X 39,5 MM (WXHXD),



Suitability for use	For connecting PROFIBUS nodes to the PROFIBUS bus cable
Transmission rate	
Transfer rate / with PROFIBUS DP	9.6 kbit/s ... 12 Mbit/s
Interfaces	
Number of electrical connections	
<ul style="list-style-type: none"> for PROFIBUS cables 	2
<ul style="list-style-type: none"> for network components or terminal equipment 	1
Type of electrical connection	
<ul style="list-style-type: none"> for PROFIBUS cables 	Integrated insulation displacement contacts for 2-core PB FC-installation cables
<ul style="list-style-type: none"> for network components or terminal equipment 	Sub-D connector (9-pin)
Type of electrical connection / FastConnect	Yes
Mechanical data	
Design of terminating resistor	Integrated resistor combination that can be selected with slide switch

Material / of the enclosure	plastic
Locking mechanism design	Screw

Design, dimensions and weight

Type of cable outlet	35° cable outlet
Width	15.8 mm
Height	54 mm
Depth	39.5 mm
Net weight	29 g

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during storage during transport 	-40 ... +70 °C
Protection class IP	IP20

Product properties, functions, components / general

Product feature	
<ul style="list-style-type: none"> silicon-free 	Yes
Product component	
<ul style="list-style-type: none"> PG connection socket strain relief 	No Yes

Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity UL approval 	Yes Yes
last modified:	10.02.2016