

SIMATIC S7, TS ADAPTER IE BASIC FOR SIMATIC
TELESERVICE, CONNECTION ON ETHERNET, POWER SUPPLY
EXT. 24V,



General information	
Engineering with	
<ul style="list-style-type: none"> • STEP 7 TIA Portal configurable/integrated as of version 	V11
<ul style="list-style-type: none"> • STEP 7 configurable/integrated as of version 	V5.4
Installation type/mounting	
Rail mounting possible	Yes
Wall mounting/direct mounting possible	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption, typ.	50 mA; Incl. TS Module Modem
Current consumption, max.	100 mA
Inrush current, max.	5.8 A
Interfaces	

Number of industrial Ethernet interfaces	1
Industrial Ethernet	
• Industrial Ethernet interface	1 x Ethernet (RJ45)
— 100 Mbps	Yes
— 1000 Mbps	No
Dimensions	
Width	30 mm
Height	100 mm
Depth	75 mm
Weights	
Weight, approx.	100 g
last modified:	13.02.2016