

# THE FL. SERIES RANGE, THE FIRST 12MM / 13MM PUSH BUTTON IN THE WORLD WITH A FULLY ILLUMINATED LENS.

Available in 12 mm and 13.5 mm standard mounting hole sizes, a unique high brightness full face illuminated switch and a non-illuminated version as a plug-in replacement for competitor products.

Designed and manufactured in France with IP67 sealing and rugged PA6.6 polyamide construction the FL.series has superb tactile feedback and vibrant single or bi-colour multi-LED illumination.

## **M**ECHANICAL

Total travel 2 mm  $\pm 0.3$ mm Operating force 5 N  $\pm 30\%$ Panel thickness 1 - 6 mm (max)

Terminal type Plug-in terminal 2.8 x 0.5 mm

Switching action Momentary
Torque 0.3 Nm

Mechanical Life (CEI 60542-5 9b) 1,000,000 cycles (max)

## ELECTRICAL

Dielectric strength 2500 VAC Insulation resistance (CEI 60512-2 3a)  $1G\Omega$ 

Contact resistance (CEI 60512-22a)  $< 50 m\Omega$  (max) Travel contact 1.2 mm  $\pm 0.3 mm$ Electrical Life (CEI 60542-5 9a) 500,000 cycles

Current rating (typical) (CEI 60542-5 10a) 400mA at 32 VAC resistive

100mA at 50 VDC resistive 125mA at 125 VAC resistive

Weld at the soldering iron: 300°C max. for 3 seconds

#### LIGHTING

Voltage 5V

It is possible to lower the voltage until 2.7V «min» to lower the luminous intensity.

Current LED 65 mA (max)

## ENVIRONMENTAL

IK impact resistance. (EN 50102)

Ingress protection (DIN EN IEC60529)

Operating temperature (CEI 60512-6)

Storage temperature (CEI 60512-6)

IK6 (front face)

IP67 (front face)

-40°C to +85°C

-40°C to +105°C

Saline mist 48 hours Cyclic temperature / humidity test «Z/AD» (CEI 6068-2-38)

240 hours (cycles of -10°C in 65°C / 93% humidity)

## Part numbers

Non-illuminated					
Ø13.5	Ø12	Cap			
FL13NN	FL12NN	Black			
FL13NB	FL12NB	Blue			
FL13NG	FL12NG	Green			
FL13NO	FL12NO	Orange			
FL13NR	FL12NR	Red			
FL13NW	FL12NW	White			
FL13NY	FL12NY	Yellow			

#### ILLUMINATED

Ø13.5	Ø12	Сар
FL13LB5	FL12LB5	Blue
FL13LG5	FL12LG5	Green
FL13LO5	FL12LO5	Orange
FL13LR5	FL12LR5	Red
FL13LW5	FL12LW5	White
FL13LY5	FL12LY5	Yellow

#### Dual-color illuminated

Ø13.5	Ø12	Сар	Illumination color
FL13DGB5	FL12DGB5	Milky white	Blue or Green*
FL13DRB5	FL12DRB5	Milky white	Blue or Red*
FL13DRG5	FL12DRG5	Milky white	Green or Red*

\*INVERTED POLARITY

### **M**ATERIALS


Body PA 6.6 Button PC

Contacts Gold plated nickel
Contacts terminals Gold plated nickel
LED terminals Silver plated nickel







# Ø13.5mm PRODUCT DRAWINGS



# PANEL CUT OUT







**Ø12mm** PRODUCT DRAWINGS




PANEL CUT OUT






Terminal version:



DIAGRAM



www.eozonline.com