

EM - Server Rack Enclosures



ACCESSIBILITY

- 1 **Removable locking side panels** for easy access.
- 2 **1U cable knockouts** on top & bottom for easy connection management.

COOLING

- 3 **Vented top** to facilitate air circulation. Use dedicated fan units (FU-EM Series).

SECURITY

- 4 **Lockable front door and back door** for maximum security (optional key locks for side panels).

EASY TO USE

- 5 **Comes with swivel castors and adjustable feet** for fast and easy installs.
- 6 **Adjustable rack rails** to adapt to your equipment and accessories.
- 7 **Front & rear rack rails.**


3 Depths & 2 Widths Available




EM-66



EM-68




EM-610



EM-88

5 Heights Available



- With their solid high end construction, the EM Rack Servers Series are a high quality solution for all of your IT and audio/visual requirements at an affordable cost.
- The locking front & back doors, removable side panels as well as cable knockouts and vented top make EM Rack Servers Series very versatile and easy to use.
- Thanks to its integrated swivel castors and adjustable feet, EM Server Racks can be turned from static to mobile in a matter of minutes.
- EM Rack Servers Series are the perfect high end solution for a low cost install.



3 Types of Rails Available





2 Types of Front Door Tempered Glass or Perforated Steel



No Assembly Required

We assembled it, so you don't have to.



U Size	Total Height (Including Castors)
22U	1157 / 45.55"
32U	1601 / 63.03"
37U	1815 / 71.46"
42U	2046 / 80.55"
47U	2268 / 89.29"

Load capacity: 500kg / 1100lbs

Door	Part Number	U Size	Width	Depth	Mounting Depth	
					Min	Max
Tempered Glass	EMS-6622BK	22U				
	EMS-6632BK	32U	600mm	616mm	142mm	450mm
	EMS-6642BK	42U	23.62"	24.25"	5.59"	17.72"
	EMS-6647BK	47U				
	EMS-6822BK	22U				
	EMS-6832BK	32U	600mm	816mm	142mm	690mm
	EMS-6842BK	42U	23.62"	32.13"	5.59"	27.16"
	EMS-6847BK	47U				
	EMS-8822BK	22U				
	EMS-8832BK	32U	800mm	816mm	142mm	690mm
	EMS-8842BK	42U	31.5"	32.13"	5.59"	27.16"
	EMS-61022BK	22U	600mm	1016mm	142mm	850mm
Perforated Steel	EMS-61032BK	32U	23.62"	40"	5.59"	33.46"
	EMS-61042BK	42U				
	EMP-6622BK	22U				
	EMP-6632BK	32U	600mm	600mm	142mm	450mm
	EMS-6637BK	37U	23.62"	23.62"	5.59"	17.72"
	EMP-6642BK	42U				
	EMP-6822BK	22U	600mm	800mm	142mm	690mm
	EMP-6832BK	32U	23.62"	31.5"	5.59"	27.16"
	EMP-6842BK	42U				