


Round Standoff / Female - Female / M4/Ø8.0X10.0 / PA/GF / black
 05.34.310

Model	Female / Female
Length	10.00 mm
Thread 1	M4
Thread 1 Length	10.00 mm
Thread 2 Length	0.00 mm
Material	Nylon, 25% glass-fiber reinforced UL94 HB
Plating / Color	Black
Undercut	no
Flammability Class	UL94 HB
Wrench Size / OD	Ø8 WS / Ø
RoHS II Compliant	yes
REACH/SVHC Free	yes

