

**Round Standoff / Female - Female / M3/Ø8.0X7.0 / PA/GF / black**
05.34.407

Model	Female / Female
Length	7.00 mm
Thread 1	M3
Thread 1 Length	7.00 mm
Thread 2 Length	0.00 mm
Material	Nylon, 25% glass-fiber reinforced UL94 V-2
Plating / Color	Black
Undercut	no
Flammability Class	UL94 V-2
Wrench Size / OD	Ø8 WS / Ø
RoHS II Compliant	yes
REACH/SVHC Free	yes

