


Round Standoff / Female - Female / M3/Ø7.0X12.0 / PA/GF / black
 05.33.212

Model	Female / Female
Length	12.00 mm
Thread 1	M3
Thread 1 Length	12.00 mm
Thread 2 Length	0.00 mm
Material	Nylon, 25% glass-fiber reinforced UL94 HB
Plating / Color	Black
Undercut	no
Flammability Class	UL94 HB
Wrench Size / OD	Ø7 WS / Ø
RoHS II Compliant	yes
REACH/SVHC Free	yes

Similar products	Round Standoff / Female - Female / M3/Ø6.0X12.0 / PA/GF / black 05.33.312
	Round Standoff / Female - Female / M3/Ø6.0X12.0 / POM / white 05.33.712

