


Round Standoff / Female - Female / M4/Ø7.0X20.0 / PA/GF / black
 05.34.820

Model	Female / Female
Length	20.00 mm
Thread 1	M4
Thread 1 Length	20.00 mm
Thread 2	M4
Thread 2 Length	0.00 mm
Material	Nylon, 25% glass-fiber reinforced UL94 HB
Plating / Color	Black
Undercut	no
Flammability Class	UL94 HB
Wrench Size / OD	Ø7 WS / Ø
RoHS II Compliant	yes
REACH/SVHC Free	yes

