

**Round Standoff / Female - Female / M3/Ø7.0X18.0 / PA/GF / black**  
05.33.218

|                    |                                           |
|--------------------|-------------------------------------------|
| Model              | Female / Female                           |
| Length             | 18.00 mm                                  |
| Thread 1           | M3                                        |
| Thread 1 Length    | 8.50 mm                                   |
| Thread 2           | M3                                        |
| Thread 2 Length    | 8.50 mm                                   |
| Material           | Nylon, 25% glass-fiber reinforced UL94 HB |
| Plating / Color    | Black                                     |
| Undercut           | no                                        |
| Flammability Class | UL94 HB                                   |
| Wrench Size / OD   | Ø7 WS / Ø                                 |
| RoHS II Compliant  | yes                                       |
| REACH/SVHC Free    | yes                                       |

**Similar products**

Round Standoff / Female - Female /  
M3/Ø6.0X12.0 / PA/GF / black  
05.33.312

Round Standoff / Female - Female /  
M3/Ø6.0X12.0 / POM / white  
05.33.712

