

**Round Standoff / Female - Female / M3/Ø7.0X15.0 / PA/GF / black**
05.33.215

Model	Female / Female
Length	15.00 mm
Thread 1	M3
Thread 1 Length	15.00 mm
Thread 2 Length	0.00 mm
Material	Nylon, 25% glass-fiber reinforced UL94 HB
Plating / Color	Black
Undercut	no
Flammability Class	UL94 HB
Wrench Size / OD	Ø7 WS / Ø
RoHS II Compliant	yes
REACH/SVHC Free	yes

Similar products

Round Standoff / Female - Female /
M3/Ø6.0X15.0 / PA/GF / black
05.33.315

Round Standoff / Female - Female /
M3/Ø6.0X15.0 / POM / white
05.33.715

