


**Round Standoff / Female - Female / M3/Ø7.0X5.00 / PA/GF / black**  
 05.33.205

<b>Model</b>	Female / Female
<b>Length</b>	5.00 mm
<b>Thread 1</b>	M3
<b>Thread 1 Length</b>	5.00 mm
<b>Thread 2 Length</b>	0.00 mm
<b>Material</b>	Nylon, 25% glass-fiber reinforced UL 94V-2
<b>Plating / Color</b>	Black
<b>Undercut</b>	no
<b>Flammability Class</b>	UL 94V-2
<b>Wrench Size / OD</b>	Ø7 WS / Ø
<b>RoHS II Compliant</b>	yes
<b>REACH/SVHC Free</b>	yes

**Similar products**

- Round Standoff / Female - Female / M3/Ø6.0X12.0 / PA/GF / black 05.33.312
- Round Standoff / Female - Female / M3/Ø6.0X12.0 / POM / white 05.33.712

