



Sample photo

Order symbol: PC 300/150 ZG
Product nbr: 6017338
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074061515
El. number:
Finland: 3435614
Denmark: 8212027983
Norway:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		360	255	152	Ingress Protection (EN 60529): IP 66/67
inch:		14.2	10.0	6.0	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			NEMA Class: NEMA 1, 4, 4X and 6
Gasket material:		Polyurethane			Certificates:
Temperatures:					Gost R
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MIV 300		Mounting plate (Galvanized steel)			
MIV 200		Mounting plate (Galvanized steel)			
MIV 150		Mounting plate (Galvanized steel)			
MIN 20		DIN-15 Mounting rail			
MIN 15		DIN-15 Mounting rail			
MIV 30		DIN-35 Mounting rail			
MIV 20		DIN-35 Mounting rail			
MIV 15		DIN-35 Mounting rail			
FP 10674		Wall fastening lug (2 pcs)			

