# HellermannTyton

## **SNP18A10C2**



Article Number: 181-00256

Snapper Hose Clamps, .776"/.929" Min/Max Diameter, POM, White, 100/pkg





#### **Base Data**

Local Order Number SNP18A10C2

Type SNP18A

Color White (WH)

Features and Benefits • Designed for quick, ratcheted installation and can be released and reused.

· Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.

Product Description HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time.

The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high

performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

Short Description Snapper Hose Clamps, .776"/.929" Min/Max Diameter, POM, White, 100/pkg

#### **Product Dimensions**

Fixation Method Plug-in mounting

Variant Closed

Width W2 (Imperial) 0.234 "

Width W2 (Metric) 5.94 mm

Diameter Min. (Imperial) 0.776 "

Diameter Min. (Metric) 19.71 mm

Diameter Max. (Imperial) 0.929 "

Diameter Max. (Metric) 23.6 mm

Wall Thickness WT (Imperial) 0.067 "

Wall Thickness WT (Metric) 1.7 mm

# **Logistics and Packaging**

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 3000

## **Material and Specifications**

Material Polyacetal (POM)

Material Shortcut POM

Flammability UL94 HB

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

