



Features:

- Direct replacement of fluorescent T8 tube
- Designed for safety with live and neutral placed at the same end
- Easy installation
- 3 Times longer than fluorescent T8 lamp

Specifications:

Lamp Base Type : T8 / G13
Average Bulb Life : 30,000 hours
Supply Voltage : 230V

Part Number Table

Description	LED Colour	Power Rating	Part Number
LED Tube, 600mm, 3000K	Warm White	10W	HK-LA201
LED Tube, 600mm, 6000K	Daylight White		HK-LA202
LED Tube, 900mm 3000K	Warm White	15W	HK-LA207
LED Tube, 900mm, 6000K	Daylight White		HK-LA208
LED Tube, 1200mm, 4500K	Cool White	18W	HK-LA210
LED Tube, 1500mm, 4500K	Cool White	21W	HK-LA221

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of the Group. © Premier Farnell plc 2012.