

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022035085

Status:


Active

Overview:

SPOX™ Wire-to-Board Connectors

Description:

2.50mm Pitch SPOX™ Wire-to-Board Header, Vertical, Shrouded, 8 Circuits, Tin (Sn) Plating



Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-5264-001 \(PDF\)](#)

[Packaging Specification SPK-5267-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	5267
Application	Signal, Wire-to-Board
Overview	SPOX™ Wire-to-Board Connectors
Product Name	SPOX™
UPC	800753734098
Physical	
Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	692.300/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/79/2015 (17

December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

[5267](#) Series

Mates With

[5264](#) SPOX™ Wire-to-Board Crimp

Housing, [42219](#) SPOX™ IDT Receptacle

Housing

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Material Info

Old Part Number	5267-08A
-----------------	----------

Reference - Drawing Numbers

Packaging Specification	SPK-5267-001
Product Specification	PS-5264-001, RPS-5264-005, RPS-5267-001
Sales Drawing	SD-5267-NA

This document was generated on 03/30/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION