



THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.



NOTE:

CLIP: .012 [0.30] THK BRASS, TIN OVER NICKEL PLATE
 BASE: MAT'L: GLASS FILLED NYLON, UL 94V-0
 VOLTAGE RATING: 500VAC
 TEMPERATURE RATING: -58°F TO +292°F
 (-50°C TO +145°C)

KEYSTONE ELECTRONICS CORP.			
ASTORIA, N.Y. 11105-2017			
PART NAME			
MINIATURE AUTO FUSE PC CLIP ASS'Y			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		BOONE	10.15.93
		APP'D	SCALE
		LN	4X
TOLERANCES	INCH [MM]	CODE	DWG NO.
DECIMAL	± .005 [± 0.15]	C	3544-2
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED			

8.25.03	CHANGE AS PER ECN 03-061	C
DATE	DESCRIPTION	REV.