

# NAUSB3-B

Reversible USB 3.0 gender changer (type A and B), black D-housing

The NAUSB3-W is a reversible USB 3.0 feed through adapter. The standardized D-shape housing of the adapter fits into conventional patch panels and offers an additional protection for the connector.



## Features & Benefits

- USB 3.0 gender changer type A-B or B-A
- Reversible insert offering type A or B on front or rear end
- Standard D-shape housing
- Removable screen for chassis grounding

## Image gallery



## Cable lengths

To ensure an error-free data transmission it is essential to use an appropriate cable with correct length. The table below lists the maximum cable length according to the wire gauge (AWG) of the used USB 3.0 cable.

Wire gauge	Cable length
AWG 20	4.5 m
AWG 22	3.5 m
AWG 24	2.0 m
AWG 26	1.2 m
AWG 28	0.75 m

## Technical Information [hide](#)

Product	
Title	NAUSB3-B
Connection Type	Adapter
Gender	female
Mechanical	
Mounting direction	front
Chassis shape	D
Material	
Contact plating	Au
Contacts	Brass (CuZn39Pb3)
Insert	PBTP 15 % GR
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Environmental	
Flammability	UL 94 V-0
Standard compliance	USB 3.0 specifications
Temperature range	-25 °C to +85 °C

Accessories

---

MFD

DSS-\*

SCDP-\*

SCDX

SCCD-W

SCD-W