



**Schneider Electric USA**  
1415 South Roselle Road  
Palatine, IL 60067  
Customer Care Center: 1-888-778-2733  
Web: [www.schneider-electric.us](http://www.schneider-electric.us)

**ITEM # ZB5AVB6, BASE & LIGHT MODULE**

Base & Light Module

|                                     |                             |   |
|-------------------------------------|-----------------------------|---|
| Specifications                      |                             | — |
| Product Description                 | Base & Light Module         |   |
| Ampere Rating                       | N/A                         |   |
| Terminal Type                       | Screw Clamp                 |   |
| Wire Range                          | min: 1x0.22; max: 2x16AWG   |   |
| Tightening Torque                   | 0.8 Nm                      |   |
| Light Module Electrical Consumption | 24V = 18mA; 120/240V = 14mA |   |
| CE                                  | Yes                         |   |
| RoHS                                | Yes                         |   |
| Contact Configuration               | n/a                         |   |
| Contact Material                    | n/a                         |   |
| Light Module Supply Voltage         | 24Vac/dc                    |   |
| Light Module Type                   | LED(blue)                   |   |
| Light Module Voltage                | 24Vac/dc                    |   |
| Utilization Category                | n/a                         |   |
| Used On                             | ZB5 Plastic Operators       |   |
| Application                         | n/a                         |   |