



### Main

Commercial Status	Commercialised
Range of product	Kaedra
Product or component type	Weatherproof enclosure
Enclosure type	Mini enclosure for modular device
Accessories included with enclosure	1 marking kit 2 terminal blocks 4 holes

### Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	6
Total number of 18 mm modules	6
Number of horizontal rows	1
Electrical insulation class	Class II Double insulation
Provided equipment	Terminal block 4 holes for 2 Marking kit for 1
Type of front cover	Transparent
Power dissipation in W	11 W
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	3
Number of terminal blocks	2 with 4 outgoers
Distribution block outgoers	4 x 16 mm <sup>2</sup> 4 x 10 mm <sup>2</sup>
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Width	159 mm
Height	200 mm
Depth	112 mm
Colour	Enclosure : light grey ( RAL 7035 ) Door : transparent green

### Environment

Standards	EN 50102 EN 50262 IEC 60439-3 IEC 60529 IEC 60695-2-1 IEC 670
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	Ultraviolet degradation test conforming to ISO 4892-2 2013 UV resistant class 3 conforming to ISO 4582 2010
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C