

# Product data sheet

## Characteristics

# NSYCRN252150

Spacial CRN plain door w/o mount.plate.  
H250xW200xD150 IP66 IK10 RAL7035..



Product availability: Stock - Normally stocked in distribution facility

Price\*: 79.24 USD



### Main

Commercial Status	Commercialised
Range of product	Spacial CRN
Device application	Multi-purpose
Product or component type	Compact enclosure
Enclosure nominal height	9.84 in (250 mm)
Enclosure nominal width	7.87 in (200 mm)
Enclosure nominal depth	5.91 in (150 mm)
Installation accessory type	Wall-mounting
Device composition	Lock 1 Door 1 Cable gland plate 1 Body 1
Door type	Plain
Mounting plate description	Without mounting plate

### Complementary

Variant particularity	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	1 front face
Door opening	Reversible 120 °
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Cable gland plate by screws Door by hinges
Material	Steel for body
Surface finish	Epoxy-polyester powder
Colour	Grey RAL 7035
Standards	IEC 62208
Product certifications	CUL UL

### Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

## Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	00785901878414
Nbr. of units in pkg.	1
Package weight(Lbs)	6.42
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	ES

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0940 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Period	18 months
--------	-----------