

Main

| | |
|-----------------------------|---|
| Commercial Status | Commercialised |
| Range of product | 9007 |
| Series name | Heavy duty |
| Product or component type | Limit switch lever |
| Device short name | 9007C |
| Associated head | 9007A 9007B 9007C 9007N 9007T10 9007T5 |
| Associated complete product | 9007AW 9007C |
| Movement of operating head | Rotary |
| Type of operator | Cast zinc spring return roller lever length: 2 in - offset: 0.44 in - |
| Type of roller | 1 steel outside roller diameter: 0.63 in - width: 0.25 in |
| Type of approach | Lateral approach |
| Positive opening | Without |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight | 0.1 lb(US) |


Environment

| | |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -20...185 °F |
| Ambient air temperature for storage | -20...185 °F |
| Environmental characteristic | Standard environment |

Ordering and shipping details

| | |
|-----------------------|---|
| Category | 21493 - 9007 ARMS FOR AW,C |
| Discount Schedule | DS1 |
| GTIN | 00785901814924 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.10 |
| Product availability | Stock - Normally stocked in distribution facility |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------------|--|
| Sustainable offer status | Not Green Premium product |
| RoHS | Will be Compliant on 3Q2014 |
| Product environmental profile | Available  Download Product Environmental |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|--------|-----------|
| Period | 18 months |
|--------|-----------|