



Product availability: Stock - Normally stocked in distribution facility

Price\*: 248.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	30 A
Product certifications	CSA UL listed
System Voltage	240 V AC
Mounting mode	Plug-in
Poles description	3P
Short-circuit current	10 kA
Number of spaces required	3
Circuit breaker type	Standard
Circuit breaker application	HACR rated
Electrical connection	Pressure plate
AWG gauge	AWG 14...AWG 8 (copper or aluminium)
Accessory / separate part type	None

### Ordering and shipping details

Category	00012 - QO 3 POLE CIRCUIT BREAKER
Discount Schedule	DE2A
GTIN	00785901400721
Nbr. of units in pkg.	3
Package weight(Lbs)	0.81
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Period	18 months
--------	-----------