

ITEM # 9001KS11BH13, PUSH BUTTONS 30 MM - ASSEMBLIES

30mm 2 Pos Sel Switch w/ contact and legend



Specifications		—
Type	Selector Switch	
Circuit Configuration	SPDT	
Actuator Type	Selector Knob	
Illumination	None	
Terminal Plating	Terminal - Brass - no plating, Screw - Zinc Chromate	
Actuator Color	Black	
Electrical Life	100000	
Mechanical Life	500000	
Operating Temperature Range	-30 to 60 °C -22 to 140 °F	
Power Rating	Not HP Rated	
Number of Poles	1 N.O. + 1 N.C.	
AC Voltage	600 V	
Current	10 A	

Contact Rating

AC-15: 600V, 1.2A; 240V, 3A; 120V, 6A DC-13: 600V, 0.1A; 250V, 0.27A; 125V, 0.55A