

Product data sheet

Characteristics

QO612L100S

LOAD CENTER QO MLO 240V 100A 1PH 6SP N1



Product availability: Stock - Normally stocked in distribution facility

Price*: 87.00 USD



Main

Commercial Status	Commercialised
Product or component type	Load Centre
Range of product	QO
Load centre type	Fixed Mains (lugs)
Line Rated Current	100 A
Number of spaces	6
Short-circuit current	10 kA
Number of circuits	12
Number of tandem circuit breakers	6
Phase	1 phase
System Voltage	120/240 V AC

Complementary

AWG gauge	AWG 8...AWG 1 (aluminium/copper)
NEMA degree of protection	NEMA 1 indoor
Cover type	Surface cover
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated aluminium busbar
Product certifications	UL listed

Ordering and shipping details

Category	00101 - QO 1PH LC,2-8CKT,NEMA 1,3R
Discount Schedule	DE3A
GTIN	00785901785576
Nbr. of units in pkg.	1
Package weight(Lbs)	7.93
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1423 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------