

70 Diagonal Cutters with tether attachment point



70 05 160 T



- 20 % higher cutting force than the previous model, plus longer cutting edges
- high cutting force due to optimum cutting geometry and transmission ratio
- strong precision rivet for even movement and long service-life
- high-precision cutting edges: additionally induction hardened, cutting-edge hardness approx. 62 HRC
- narrow head with long cutting edges: good access also in confined areas
- long tool life and high loading capacity
- the essential diagonal cutters for diverse use
- Vanadium steel, forged, oil-hardened in multiple steps

70 05 160 T:

- Pliers with tether attachment point for mounting a fall protection

Article No.	EAN		Pliers	Handles	Ø mm	Ø mm	Ø mm	mm	g
70 05 160 T	4003773-080022		chrome plated	with multi-component grips	4,0	3,0	2,0	160	210

technical change and errors excepted