

71 02 200 T

KNIPEX CoBolt® with tether attachment point with tether attachment point



- precision cutting edges for soft and hard wire as well as piano wire
- cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- most efficient joint design ensures exceptional cutting performance
- cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, oil-hardened
- Pliers with tether attachment point for mounting a fall protection



60 % less effort required compared to conventional high-leverage diagonal cutters

The ingenious lever-action mechanism ensures an extremely favourable lever ratio with very little friction. The cutting force is about 20 times higher than the hand force applied.

Article No.	71 02 200 T
EAN	4003773080046
Pliers	black atramentized
Handles	with slim multi-component grips
Style	0
soft wire Ø mm	6,0
medium hard wire Ø mm	5,2
hard wire Ø mm	4,0
piano wire Ø mm	3,6
Length mm	200
Net weight g	375

technical change and errors excepted