

74 02 200 T

High Leverage Diagonal Cutter with tether attachment point



- for very tough, continuous use
- high cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- precision cutting edges additionally induction hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, oil-hardened
- Pliers with tether attachment point for mounting a fall protection



20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.

Article No.	74 02 200 T
EAN	4003773080084
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Style	0
medium hard wire Ø mm	4,2
hard wire Ø mm	3,0
piano wire Ø mm	2,5
Length mm	200
Net weight g	305



technical change and errors excepted