

SCA100T-D01

Specifications

Output Type	Analog/SPI
Axis	2
Maximum Angular Velocity	$\pm 0.5g \pm 30deg$
Supply Voltage	5V
Offset Temp. Characteristic	$\pm 0.86deg$
Sensitivity	4V/G
Amplitude Response	18Hz
Mass	1.01g

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.