

GA355DR7GC472KY02#

" # " indicates a package specification code.

To be discontinued

General

Safety standard

125℃


Reflow OK


RoHS

REACH

< List of part numbers with package codes >  
GA355DR7GC472KY02L

Shape





L size	5.7 ± 0.4mm
W size	5.0 ± 0.4mm
T size	2.0 ± 0.3mm
External terminal width e	0.3mm min.
Distance between external terminals g	4.0mm min.
Size code in inch(mm)	2220 (5750)

Notes

Please use replacements or Recommended.

References

Packaging	Specifications	Minimum quantity
L	180mm Embossed taping	1000

Mass (typ.)	
1 piece	290mg
180mm Reel	347g

Specifications

Capacitance	4700pF ± 10%
Rated voltage	250Vac
Temperature characteristics (complied standard)	X7R(EIA)
Capacitance change rate	± 15.0%
Temperature range of temperature characteristics	-55 to 125
Operating temperature range	-55 to 125

⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.