

DECB33J101KC4B

"#" indicates a package specification code.














< List of part numbers with package codes > DECB33J101KC4B

Shape



References

Packaging	Specifications	Minimum quantity
В	Packing in bulk	250

Specifications

Capacitance	100pF ± 10%
Rated voltage	6300Vdc
Temperature characteristics (complied standard)	B(JIS)
Capacitance change rate	± 10%
Temperature range of temperature characteristics	-25 to 85
Operating temperature range	-25 to 85

1 of 1

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it 's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Murata Manufacturing Co., Ltd.

URL: http://www.murata.com/

Last updated: 2015/12/04