

DEC1X3J220JC4B



< List of part numbers with package codes > DEC1X3J220JC4B

Shape

e F G g d g d g d g d g d g d g d g d g d g	
L size or outer diameter D (mm)	9.0 mm max.
T size	7.0 mm max.
Lead spacing F	10.0 ± 1.0mm
Lead diameter d	0.6 ± 0.05mm
Paint dripping e	3.0mm max.

Specifications

Capacitance	22pF ±5%
Rated voltage	6300Vdc
Temperature characteristics (complied standard)	SL(JIS)
Temperature coefficient	+350 to -1000ppm/
Temperature range of temperature characteristics	20 to 85
Operating temperature range	-25 to 85

References

"# " indicates a package specification code.

Packaging	Specifications	Minimum quantity
В	Packing in bulk	250


1 of 1

🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it 's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



URL : http://www.murata.com/

Last updated: 2015/12/04