


Datasheet

Art.No. 80.063.4001.1

Screw terminal socket FLARE MOVE SF38 24V DC

relais holder frare MOVE , supply vottage 24 VDC, screw clamp terminal, width 6,2 mm type: flare MOVE SF38 24V DC



Approvals



Technical data

General

Connection type	Screw connection
Detachable clamps	No
Number of pins	5
Mounting method	TS35
Function extension possible	No

Dimensions

Depth	76 mm
Width	6.2 mm
Height	88 mm

Classification

ECLASS 8.1	27371603: Relay socket
ETIM 5.0	EC001456: Relay socket
ETIM 4.0	EC001456: Relay socket
ETIM 3.0	EC001456: Relay socket