


# DEBB33F221KCDB

In Production	General	<b>85</b>	Flow OK	RoHS	REACH
---------------	---------	-----------	---------	------	-------

< List of part numbers with package codes > DEBB33F221KCDB

## Shape



# Specifications

Capacitance	220pF ±10%	
Rated voltage	3150Vdc	
Temperature characteristics (complied standard)	B(JIS)	
Capacitance change rate	± 10%	
Temperature range of temperature characteristics	-25 to 85	
Operating temperature range	-25 to 85	

References
------------

"# " indicates a package specification code.

Packaging	Specifications	Minimum quantity	
В	Packing in bulk	500	


#### 1 of 1

## 🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it 's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



URL : http://www.murata.com/

Last updated: 2015/12/04