

Datasheet

Art.No. 80.020.4101.0

Solid state relay FLARE-24VDC/48VDC-2A

flare, solid state relay with 6,2 mm overall width, output, transistor module, spring clamp terminal, input: 24 V DC, output: 4,4 - 53 V DC/2 A, jumper At negative pole At the controll side , type: flare-24VDC/48VDC-2A



Approvals



Technical data

General

Modular version	No
-----------------	----

Technical data

Connection type	Tension clamp connection
Type of excitation	
Min. connection voltage	4.4 V
Max. connection voltage	53 V
Rated operating current DC	2 A
Min. control voltage	10 V
Max. control voltage	53 V

Dimensions

Depth	70 mm
Width	6.2 mm
Height	89 mm

Classification

ECLASS 8.1	27371014: Solid state relay
ETIM 5.0	EC002055: Solid state relay
ETIM 4.0	EC002055: Solid state relay
ETIM 3.0	EC002055: Solid state relay