

DHRB34C471M2BB

" # " indicates a package specification code.

Recommended

In Production

General

100℃

Ultrahigh-voltage

Deflecting crack

Soldering crack


FlowOK

RoHS

REACH

< List of part numbers with package codes >  
DHRB34C471M2BB

Shape



(in mm)

L size or outer diameter D (mm)	13.0 mm max.
T size	8.2 mm max.
Lead spacing F	9.5 ± 2.0mm
Lead diameter d	0.65 ± 0.05mm
Paint dripping e	4.0mm max.

References

Packaging	Specifications	Minimum quantity
B	Packing in bulk	200

Specifications

Capacitance	470pF ± 20%
Rated voltage	15kVdc
Temperature characteristics (complied standard)	B(JIS)
Capacitance change rate	± 10%
Temperature range of temperature characteristics	-25 to 85
Operating temperature range	-25 to 100

⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.