

Feeler Gauge

MPN: n/a



Order No	950-251	950-252	950-254	950-255	950-256
Range	.002-.035in	.0015-0.025in	.0015-.200in	.0015-.200in	.0015-.015in
# of Leaves	26	26	15	13	8
Length	3in	3in	3in	4 1/2in	6in
Composition	0.02 thru 0.18" by 0.01" step plus .022, .024, .025, .028, .030, .032, .035"	.002 thru .025" by .001" step plus .0015, .0025"	0.015, 0.02, 0.03, 0.04, 0.06, 0.08, 0.10, 0.12, 0.15, 0.20, 0.30, 0.40, 0.75, .100, .200"	0.015, 0.02, 0.03, 0.04, 0.06, 0.08, 0.10, 0.20, 0.30, 0.40, 0.75, .100, .200"	0.015, 0.02, 0.03, 0.04, 0.08, 0.10, 0.12, 0.15"
Type of Blade	Straight 1/2in width	Tapered 1/4 width at tip	Straight 1/2in width	Straight 1/2in width	Straight 1/2 width