

MultiPhones **Prestigio Muze A5 - PSP5502DUOGUNMETAL**



DISPLAY	
Display Size	5"   12.7 cm
Display Resolution	720x1280
Pixel Density	294 ppi
Display Technology	IPS
Display Color Depth	16M
PROCESSOR	
CPU Internal Clock Rate	1.20 GHz
CPU Core Quantity	4
MEMORY*	
Internal Memory Size	8 GB
Installed RAM Storage Capacity	1 GB
Supported Flash Card	Micro SD up to 32GB
SOFTWARE	
Platform	Android
Operating System Version	Android 5.1
CAMERA	
Camera Resolution	8.0 Mpixel

Flash	Yes
Front Camera	2.0 Mpixel
<b>INTERFACES</b>	
Bluetooth	Yes
Wi-Fi	Yes
Data Interface	Micro USB
Audio	3.5mm mini-jack
<b>MULTIMEDIA</b>	
Supported Multimedia	Audio Playback, Video Playback, Picture, Text, Games
<b>MISCELLANEOUS</b>	
Construction	Monoblock
External Colour	Black / Gunmetal
SIM Card	Dual Sim
Package Type	Retail
<b>BATTERY**</b>	
Battery Capacity	2000 mAh
Battery Technology	Lithium Ion
<b>WARRANTY</b>	
Warranty Products Returnable	Yes
Warranty Term (month)	12 month(s)
Warranty Validation Criteria	Serial Number

*\* User memory is less than the total memory due to storage of the operating system and software used to operate the phones features. Actual user memory will vary depending on the mobile phone operator and may change after software upgrades are performed.*

*\*\* The results received are based on our company`s tests. Please note, that the data may vary due to the specific reasons.*