This document was generated on 04/13/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0191600009
Status: Active
Overview: Splices
Description: Closed-End Insulated Splice for 12-22 AWG Wire

Series image - Reference only

Documents:

Drawing (PDF)
Product Specification PS-19902-013 (PDF)
Packaging Specification PK-19408-109 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	19160
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	Splices
Product Name	Closed-End Insulated
UPC	800753110182

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.689/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	6.86mm max.
Wire Size AWG	12, 14, 16, 18, 20, 22

Electrical

Voltage - Maximum	600V

Material Info

Old Part Number	NC-2212

Reference - Drawing Numbers

Packaging Specification	PK-19408-109
Product Specification	PS-19902-013
Sales Drawing	SD-19160-001

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series
19160 Series

Application Tooling | **FAQ**

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0640010900
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050900
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640053600

This document was generated on 04/13/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION