


## **50W Constant Voltage LED Driver Series**



## Dimension in mm





## Reliable Technical Data

- Rated Input Voltage:200-240VAC
- Input Frequency:50Hz
- Output Power:50W
- Dimension:L185xW63.5xH22mm
- Body:PC
- · Open Circuit; Short Circuit; Over Load;
- · Over Heat Protection
- Safety According to EN61347-1,EN61347-2-13
- . EMI According to EN55015
- EMS According to EN61000-3-2;EN61000-3-3;EN61547
- · Approbation Mark:CE ROHS;TUV;C-Tick



## ■ Characteristics

Rated input voltage: AC200-240V 50Hz (power factor measured at AC230V and full load)

Model No.	Constant out Voltage	Load	Max output Current	PF	Ta	Tc	L×W×H	Approval
LED-DR-12V-4000-60	12V	0-50W	4.17A	0.9	45℃	80℃	185X63.5X22	TUV
LED-DR-24V-2080-50	24V	0-50W	2.08A	0.9	45℃	80℃	185X63.5X22	TUV