



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™



LAN PRONAVIGATOR® TESTER & REMOTE

LAN PRONAVIGATOR® TESTER & REMOTE LAN ProNavigator test set (main & remote), 2 RJ45 patch cords, 2 belt clips, 12 oz.(342 g)

Cat No: 52046963

UPC No: 769328108149

Description

- Simple PASS/FAIL test results in one second allows technicians to quickly move on to the next test site
- Generates oscillating audio tone for use with tone probes to locate cables
- Tests data and telephone cables up to 320 feet (100 meters) for proper pairing for EIA/TIA-568A, EIA/TIA-568B, Token Ring, 10 Base T, and common Category 5 configurations
- Tests unshielded UTP and shielded STP data cable
- Detects good connections, open connections, crossed wires and split pairs
- Tests common BNC connected 50 and 75 ohm coaxial cables up to 320 feet (100 meters) for continuity
- Tests coaxial cable types RG58, RG59, RG6, RG6 Quad, Belden 8281, RG8, RG11 and more
- Belt clips provided and lanyard holes embedded in case to attach to belt or wrist
- Features low battery test and auto-off function to preserve battery life
- Includes standard 9V battery

Specifications

- Application : For Use With Tone Probes To Locate Cables
- Dimensions : 8.500 IN X 7.600 IN X 3.000 IN
- Includes : 2 RJ45 Patch Cords, 2 Belt Clips, 342 GM
- Sub Brand : LAN ProNavigator
- Weight : 2.000 OZ (1140.000 GM)