

2-conductor ground terminal block

Item No.: 282-107



2-conductor ground terminal block

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	282-107
GTIN / EAN	4045454084523
Content	1
Order amount	50
Customer item number	

Notes


Technical data



Miscellaneous

Total number of connection points	2
Total number of potentials	1
Color	green-yellow
Ratings according to 1	IEC/EN 60947-7-2
Connection technology (1)	CAGE CLAMP®
Solid sizes 1	0.2 ... 6 mm ² / 24 ... 10 AWG
Fine-stranded wires 1	0.2 ... 6 mm ² / 24 ... 10 AWG
Strip length 1	12 ... 13 mm / 0.47 ... 0.51 in
Type of wiring	Side-entry wiring
Design	horizontal

Technical data	
<i>Marking level</i>	<i>Side marking</i>
<i>Insulating material</i>	<i>Polyamide 66 (PA 66)</i>
<i>Weight [g]</i>	<i>18.987 [g]</i>
<i>Width</i>	<i>8 mm / 0.315 in</i>
<i>Height from upper-edge of DIN-rail [mm]</i>	<i>37 [mm]</i>
<i>Height from upper-edge of DIN-rail</i>	<i>37 mm / 1.457 in</i>
<i>Length</i>	<i>46.5 mm / 1.831 in</i>
<i>Type of mounting</i>	<i>DIN 35 rail</i>

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.