






**PROLINE G2**




|                                                                                                        |                                                                                                        |                                                                                                        |
|--------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|
| <p>1</p>  <p>(1x)</p> | <p>2</p>  <p>(4x)</p> | <p>3</p>  <p>(1x)</p> |
|--------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|






4X




2

2.5±0.3 N\*M  
[22±2.2 LBF-IN]



4X



3

